Note, this list is for all countries excluding the USA and country members of the European Patent Convention. For details of patents held in the USA and Europe, see separate information on the <u>Patents</u> page.

Patents:

Title	Protection Type	Country	Registration Number	Status
METHOD OF MOLDING A FIBRE-REINFORCED				
COMPOSITE WHEEL	Patent (National)	Australia	2009290123	Granted
ATTACHMENT ARRANGEMENT FOR COMPOSITE	Patent (National)	Australia	2012261644	Granted
WHEELS	Patent (National)	Japan	6068458	Granted
	Patent (National)	China	ZL 2012800326217	Granted
	Patent (National)	Republic of Korea	10-1534091	Granted
	Patent (National)	Hong Kong	HK1192519	Granted
FACE TO HUB CONNECTION FOR A COMPOSITE	Patent (National)	Australia	2012261712	Granted
WHEEL	Patent (National)	Republic of Korea	10-2015-7017650	Pending
	Patent (National)	Japan	6126696	Granted
	Patent (National)	China	ZL 201380072525X	Granted
	Patent (National)	Hong Kong	HK1211266	Pending
FACE TO RIM CONNECTION FOR A COMPOSITE	Patent (National)	Australia	2013204015	Granted
WHEEL	Patent (National)	China	ZL 2013800755664	Granted
	Patent (National)	Japan	6235118	Granted
	Patent (National)	Republic of Korea	10-2015-7032171	Pending
	Patent (National)	Hong Kong	HK1213531	Granted
EDGE ARRANGEMENT FOR A COMPOSITE WHEEL				
	Patent (Innovation)	Australia	2012101896	Granted
CENTRE-LOCK ATTACHMENT ARRANGEMENT FOR	Patent (National)	Australia	2014311253	Granted
COMPOSITE WHEELS	Patent (National)	China	ZL 2014800479052	Granted
	Patent (National)	Japan	2016-537049	Granted
METHOD OF PRODUCING THERMALLY PROTECTED	Patent (National)	Australia	2016202603	Granted
COMPOSITE	Patent (National)	China	201680023803	Pending
	Patent (National)	Japan	2018-506460	Pending

		ATTACHMENT ARRANGEMENT FOR COMPOSITE WHEELS	FACE TO HUB CONNECTION FOR A COMPOSITE WHEEL	FACE TO RIM CONNECTION FOR A COMPOSITE WHEEL	EDGE ARRANGEMENT FOR A COMPOSITE WHEEL	CENTRE-LOCK ATTACHMENT ARRANGEMENT FOR COMPOSITE WHEELS	METHOD OF PRODUCING THERMALLY PROTECTED COMPOSITE	CR9 Front	CR9 Rear	CR10
AS_Customer Part							001111 001112			
Number	Description									
AS-003	CR9-3 19x8.5 +53 5x130 71.6CB-CLEAR NO TBC (SF)	√	✓	√	✓			✓		<u> </u>
AS-004	CR9-3 19x12 +68 5x130 71.6CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				✓	
AS-006	CR9-3 19x8.5 +38 5x112 57.1CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-007	CR9-3 19x10.5 +23 5x120 72.5CB-CLEAR NO TBC (DF)	✓	✓	✓	✓				✓	<u> </u>
AS-008	CR9-3 19x9.5 +28 5x120 72.5CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				✓	
AS-009	CR9-3 19x12 +53 5x112 57.1CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				✓	
AS-011	CR9-3 19x8.5 +53 10x130 CL 84CB-CLEAR NO TBC (SF)		✓	✓	✓	✓		✓	✓	
AS-012	CR9-3 19x12 +63 10x130 CL 84CB-CLEAR NO TBC (MF)		✓	✓	✓	✓			✓	
AS-014	CR9-3 19x12 +45 10x130 CL 84CB-CLEAR NO TBC (DF)		✓	✓	✓	✓			✓	
AS-015	CR9-3 19x8.5 +43 5x120.6 70.3CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-016	CR9-3 19x12 +58 5x120.6 70.3CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				✓	
AS-018	CR9-3 19x10.5 +49 5x130 71.6CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				√	
AS-019	CR9-3 19x5 +13.5 5x107.95 63.34CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-020	CR9-3 19x8.5 +41 5x115 70.27CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-021	CR9-3 19x12 +50 5x130 71.6CB-CLEAR NO TBC (DF)	✓	✓	✓	✓				✓	
AS-022	CR9-3 19x8.5 +44 5x112 57.1CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-023	CR9-3 19x12 +42 5x120 72.5CB(DF)	✓	✓	✓	✓				√	
AS-024/FR3V-1007-MC	CR7-1 19x11 +24 5x114.3 70.565CB-BLACK + TBC	✓	✓	✓	✓		✓			
AS-025/FR3V-1007-NC	CR7-1 19x11.5 +56 5x114.3 70.565CB-BLACK NO TBC	✓	✓	✓	✓					
AS-027	CR9-3 19x9.5 +28 5x112 57.1CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				√	
AS-028	CR9-3 19x10.5 +41 5x120 72.5CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				√	
AS-029	CR9-3 19x9.5 +36 5x120 72.5CB-CLEAR NO TBC (MF)	✓	✓	✓	✓				√	
AS-030	CR9-3 19x10.5 +36 5x114.3 66.1CB-CLEAR WITH TBC (MF)	✓	✓	✓	✓		✓		√	
AS-031	CR9-3 19x10.5 +31 5x114.3 66.1CB (DF)	✓	✓	✓	✓			✓		
AS-036	CR9-3 19x8.5 +54 5x114.3 66.1CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓		
AS-040	CR9-3 19x8.5 +35 5x120 72.5CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			√		
AS-041	CR9-3 19x8.5 +40 5x120 72.5CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			√		
AS-043	CR9-3 19x8.5 +53 5x130 71.6CB-CLEAR WITH TBC (SF)	✓	✓	✓	✓		√	√		
AS-044	CR9-3 19x12 +68 5x130 71.6CB-CLEAR WITH TBC (MF)	✓	√	✓	✓		√		√	
AS-045	CR9-3 19x8.5 +38 5x112 57.1CB-CLEAR WITH TBC (SF)	✓	√	√	√		√	√		
AS-046	CR9-3 19x10.5 +23 5x120 72.5CB-CLEAR WITH TBC (DF)	✓	√	√	✓		√		√	
AS-047	CR9-3 19x9.5 +28 5x120 72.5CB-CLEAR WITH TBC (MF)	✓	√	✓	√		✓		✓	
AS-048	CR9-3 19x12 +53 5x112 57.1CB-CLEAR WITH TBC (MF)	✓	√	√	√		√		√	
AS-049	CR9-3 19x8.5 +53 10x130 CL 80CB-CLEAR WITH TBC (SF)		√	✓	✓	✓	✓	√		

AS-050	CR9-3 19x12 +63 10x130 CL 80CB-CLEAR WITH TBC (MF)		✓	_	✓	✓	✓		√
AS-051	CR9-3 19x12 +45 10x130 CL 80CB-CLEAR WITH TBC (DF)		✓	✓	✓	✓	✓		√
AS-052	CR9-3 19x8.5 +43 5x120.6 70.3CB-CLEAR WITH TBC (SF)	√	✓	√	✓		√	✓	
AS-053	CR9-3 19x12 +58 5x120.6 70.3CB-CLEAR WITH TBC (MF)	✓	✓	√	✓	<u></u>	✓		√
AS-054	CR9-3 19x10.5 +49 5x130 71.6CB-CLEAR WITH TBC (MF)	√	✓	✓	√		✓		√
AS-055	CR9-3 19x12 +50 5x130 71.6CB-CLEAR WITH TBC (DF)	√	✓	✓	√		✓		√
AS-058	CR9-3 19x9.5 +36 5x120 72.5CB-CLEAR WITH TBC (MF)	√	✓	✓	✓		✓		√
AS-061	CR9-3 20x10.5 +36 5x114.3 66.1CB-CLEAR WITH TBC (MF)	√	✓	✓	√		✓		✓
AS-081	CR9-3 19x12 +41 5x108 63.319CB-CLEAR NO TBC (DF)	√	✓	✓	✓				✓
AS-082	CR9-3 19x9.5 +12 5x108 63.319CB-CLEAR WITH TBC (MF)	√	✓	✓	√		✓		✓
AS-083	CR9-3 19x10.5 +41 5x120 72.5CB-CLEAR WITH TBC (MF)	√	✓	✓	✓		✓		✓
AS-087	CR9-3 19x8.5 +30 5x110 65CB-CLEAR NO TBC (SF)	✓	✓	√	✓			✓	
AS-088	CR9-3 19x9.5 +39 5x110 65CB-CLEAR NO TBC (MF)	√	✓	✓	✓				✓
AS-092/P115026162AC	CR10-3 20x8.5 +51.5 5x114.3 70.565CB-GLOSS CLEAR	√	✓	✓	✓				
AS-093/P125026162AC	CR10-3 20x11.5 +50.5 5x114.3 70.565CB-GLOSS CLEAR	√	✓	✓	✓				
AS-098/HR3V-1A145-MB	CR7-1 19x11 +24 5x114.3 70.565CB-BLACK + TBC	√	✓	✓	√		✓		✓
AS-099/HR3V-1A145-NB	CR7-1 19x11.5 +56 5x114.3 70.565CB-BLACK NO TBC	√	✓	✓	✓		✓		
AS-102	CR9-3 19x9.5 +36 5x130 71.6CB-CLEAR WITH TBC (MF)	✓	✓	√	✓		✓		√
AS-104	CR9-3 19x9.5 +36 10x130CL 84CB-CLEAR WITH TBC (MF)		✓	✓	√	✓	✓		✓
AS-106	CR9-3 19x10.5 +36 5x120 72.5CB-CLEAR WITH TBC (DF)	√	✓	✓	√		✓		✓
AS-109	CR9-3 19x10.5 +49 5x120 72.5CB-CLEAR WITH TBC (MF)	✓	✓	√	✓		✓		✓
AS-112	CR9-3 19x12 +40 5x114.3 66.1CB-CLEAR WITH TBC (DF)	✓	✓	√	✓		✓		✓
AS-113	CR9-3 19x8.5 +45 5x107.95 63.319CB-BLK-CLEAR WITH TBC (SF)	√	√	√	√		√	1	
AS-114/P115026161AC	CR10-3 20x8.5 +51.5 5x114.3 70.565CB-MATTE CLEAR	√	✓	✓	✓				
AS-115/P125026161AC	CR10-3 20x11.5 +50.5 5x114.3 70.565CB-MATTE CLEAR	✓	✓	✓	✓				
AS-116/094013184	CR9-3 20x10.5 +36 5x114 67.04CB-CLEAR WITH TBC (MF)	✓	✓	✓	✓				✓
AS-120	CR9-3 19x8.5 +30 5x110 65CB-CLEAR WITH TBC (SF) [Alfa Romeo]	✓	√	√	√		√	✓	
AS-121/00342906	CR10-5 20x9 +44.7 5x114 67.04CB-CLEAR WITH TBC	✓		✓	✓		✓		
AS-122/00342907	CR10-5 20x11 +38.5 5x114 67.04CB-CLEAR WITH TBC	✓		✓	✓		✓		
AS-124	CR9-3 19x12 +40 5x120.6 70.3CB-CLEAR WITH TBC (DF)	✓	✓	✓	✓		✓		✓
AS-130/HR3V-1A145-MC	CR7-1 19x11 +24 5x114.3 70.565CB-BLACK + TBC with Twin Ring BP	√	✓	√	✓		√		
AS-131/HR3V-1A145-NC	CR7-1 19x11.5 +56 5x114.3 70.565CB-BLACK NO TBC with Twin Ring BP	✓	√	√	√		√		
AS-132	Tesla model S 8.5" proto wheel trial	✓	✓	✓	✓			✓	
AS-133	CR9-3 19x5 +13.5 5x114.3 67CB-CLEAR NO TBC (SF)	✓	✓	✓	✓			✓	
AS-134	CR9-3 19x10.5 +28.3 5x120.65 70.3CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		✓
AS-135	CR9-3 19x12 +51.65 5x120.65 70.3CB-CLEAR WITH TBC	✓	✓	✓	✓		✓	✓	
AS-139/00848628	CR10-6 20x9.5 +43.3 5x114 67.04CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		
AS-140/00848639	CR10-6 20x11.5 +35.9 5x114 67.04CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		

AS-145/403007889R	CR9-3 19x8.5 +54 5x114.3 66.1CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		
AS-151/00342906	CR10-5 20x9 +44.7 5x114 67.04CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		
AS-152/00342907	CR10-5 20x11 +38.5 5x114 67.04CB-CLEAR WITH TBC	√	✓	✓	✓		√		
AS-155	CR9-3 19x9.5 +11 5x114.3 67CB-CLEAR WITH TBC (MF)	√	✓	✓	✓			✓	
AS-156/KR3V-1A145-MB	CR7-2 20x11 +32 5x114.3 70.565CB-CLEAR WITH TBC	√	✓	✓	✓		√		
AS-157/KR3V-1A145-NB	CR7-2 20x11.5 +50 5x114.3 70.565CB-CLEAR NO TBC	√	✓	✓	✓				
AS-160/403007889R	CR9-3 19x8.5 +54 5x114.3 66.1CB-CLEAR WITH TBC (SF)	✓	✓	✓	✓		✓	✓	
AS-161/P115026162AD	CR10-3 20x8.5 +51.5 5x114.3 70.565CB-GLOSS CLEAR	√	✓	✓	✓				
AS-162/P125026162AD	CR10-3 20x11.5 +50.5 5x114.3 70.565CB-GLOSS CLEAR	✓	✓	✓	✓				
AS-165/00866267	CR10-5 20x9 +44.7 5x114 67.04CB-CLEAR WITH TBC	✓	✓	✓	✓		✓		
AS-166/00866268	CR10-5 20x11 +38.5 5x114 67.04CB-CLEAR WITH TBC	√	✓	✓	✓		√		
AS-171/KR3V-1A145-MC	CR7-2 20x11 +32 5x114.3 70.565CB-CLEAR WITH TBC	√	✓	✓	✓	·	√		
AS-172/KR3V-1A145-NC	CR7-2 20x11.5 +50 5x114.3 70.565CB-CLEAR NO TBC	√	✓	✓	√				